

Slimline Front Panel Valve - Dry Media

LCN152N

Enware's Slimline laboratory front panel valves are assembled for each specific media type.

The durable powder coat finish gives significant protection against corrosion, discolouration and surface damage.

Slimline handles are ergonomically designed for precise feel and finger tip control. Handles are colour coded for easy service identification and use complimentary buttons.

All front panel valves are designed to be compact and easy to install and have a range of complimentary outlet options to choose from.

FEATURES

- Suited for dry media up to technical gas level 4.0
- Teflon needle valve with stainless steel seat
- Durable powder coat finish
- Handle and indicator button identification to suit specified media



Product Codes


LCN152NM Needle Valve - 1/4" BSPT

Technical Information

Inlet / Outlet Connection	1/4" BSPT
Recommended Maximum Working Pressure - Needle Valve	700 kPa (dry media)
Maximum Testing Pressure	1000 kPa
Burning Gas Options	Argon, Carbogen, Carbon Dioxide, Compressed Air, Helium, Hydrogen, Nitrogen, Nitrous Oxide, Oxygen, Vacuum. <i>Note: Client to specify media type</i>

NOTE: Enware Australia advises:

1. Due to ongoing Research and Development, specifications may change without notice.
2. Component specifications may change on some export models.
3. Refer to Warranty Statement for warranty details - www.enware.com.au/warranty



Version: Sep 21

Call 1300 369 273
www.enware.com.au

Enware Australia Pty Limited
9 Endeavour Rd Caringbah NSW 2229 Australia
Ph: 02 8536 4000 info@enware.com.au

